




**Motion detector IR for corridor, wall mounted, white**

EE880



**Technical Features**

**Detection**

Detection angle	360 - 360
Type of sensor	Movement detector

**Settings**

Time delay	5 S - 15 Min
------------	--------------

**Lighting**

Response brightness adjustable	2 - 1000 lx
--------------------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Dimensions**

Width	123 mm
Recommended installation height	3 - 3 m

**Use conditions**

Operating temperature	-20 - 50 °C
-----------------------	-------------

**Materials**

Colour	White
Material	Acrylonitrile-Butadiene-Styrene (ABS) Polycarbonate (PC) Plastic

**Safety**

Ingress Protection (IP) class	IP54
-------------------------------	------

**Installation, mounting**

Mounting on	Surface mounting
Suitable for outdoor usage	Yes

**Texts**

Function	Parallel connection of several detectors in order to expand the detection area
Installation mode	For ceiling mounting