



TYFS120\_AVANT

**KNX/IP Secure interface, 1 module**

**Technical Features**

**Equipment**

|            |    |
|------------|----|
| Web server | No |
|------------|----|

**Voltage**

|                            |           |
|----------------------------|-----------|
| Operating voltage          | 24 - 24 V |
| Operating voltage over bus | 21 - 32 V |
| Type voltage supply        | DC        |

**Settings**

|                              |     |
|------------------------------|-----|
| Supported configuration mode | ETS |
|------------------------------|-----|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Equipment**

|                    |   |
|--------------------|---|
| Number of channels | 8 |
|--------------------|---|

**Use conditions**

|                       |            |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

**Controls and indicators**

|                     |     |
|---------------------|-----|
| With LED indication | Yes |
|---------------------|-----|

**Dimensions**

|                       |   |
|-----------------------|---|
| Number of width units | 1 |
|-----------------------|---|

**Connection**

|                     |      |
|---------------------|------|
| Connector/plug type | RJ45 |
|---------------------|------|

**Texts**

|                    |                                                                                                       |
|--------------------|-------------------------------------------------------------------------------------------------------|
| Type of connection | Operating voltage connection via connecting terminal<br>With RJ45 connection for Ethernet/IP networks |
|--------------------|-------------------------------------------------------------------------------------------------------|

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |