



6765766089

Soc.out. earth. pin, enhncd contact prot.,screw-in lift term.,Q.x,p.wh.velv.

#### Technical Features

##### Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

##### Voltage

|                 |             |
|-----------------|-------------|
| Rated voltage   | 250 V       |
| Nominal voltage | 250 - 250 V |

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

##### Materials

|                |             |
|----------------|-------------|
| Colour         | Polar white |
| RAL code       | 9010        |
| Surface finish | Velvety     |
| Material       | Duroplastic |
| Treatment      | Untreated   |

##### Dimensions

|                                    |       |
|------------------------------------|-------|
| Height                             | 71 mm |
| Width                              | 71 mm |
| Number of units                    | 1     |
| Built-in depth flush-mounted boxes | 31 mm |
| Built-in depth                     | 32 mm |

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Connectivity

|                    |                                 |
|--------------------|---------------------------------|
| Type of connection | Screw terminal                  |
| Mounting type      | Screw mounting<br>Claw mounting |

##### Equipment

|                                   |              |
|-----------------------------------|--------------|
| Connector/plug type socket outlet | Earthing pin |
| Rotated central insert            | No           |
| With hinged lid                   | No           |
| With round protective earth pin   | Yes          |
| With signal lamp                  | No           |
| With lock                         | No           |

##### Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

##### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

##### Safety

|                                  |      |
|----------------------------------|------|
| With enhanced contact protection | Yes  |
| Impact resistance IK             | IK02 |
| Ingress Protection (IP) class    | IP20 |

##### Functions

|                           |    |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting    | No |

##### Texts

|                    |                              |
|--------------------|------------------------------|
| Imprint            | Without imprint              |
| Cover              | Central cover plate          |
| Protection         | Enhanced contact protection  |
| Type of connection | With screw-in lift terminals |

|                       |     |
|-----------------------|-----|
| <b>Suitable for</b>   |     |
| Q.x                   |     |
| <b>Sustainability</b> |     |
| Halogen free          | Yes |
| RoHS conform          | Yes |