



6765107006



Soc.out. earth.pin+LED orient.,enhncd contact prot.,screw-in lift term.,K.1,ant.

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Anthracite  
RAL code 7021  
Surface finish Matt  
Material Thermoplastic  
Treatment Untreated

**Dimensions**

Height 71 mm  
Width 71 mm  
Number of units 1  
Built-in depth 32 mm

**Installation, mounting**

Mounting on Flush mounting

**Connectivity**

Type of connection Screw terminal  
Mounting type Screw mounting  
Claw mounting

**Equipment**

Connector/plug type socket outlet Earthing pin  
Rotated central insert No  
With hinged lid No  
With round protective earth pin Yes  
With signal lamp No  
With lock No

**Accessories**

Has labelling field No

**Capacity**

Number of modules 1

**Controls and indicators**

Type of lighting for the installation devices Integrated orientation light

**Safety**

With enhanced contact protection Yes  
Impact resistance IK IK05  
Ingress Protection (IP) class IP20

**Functions**

With orientation lighting Yes  
With function lighting No

**Identification**

With imprint No

---

**Texts**

Cover	Central cover plate
Lighting	Additional benefit by combination of a socket outlet with an orientation light
Wiring	Through-wiring possible, therefore also ideal for retrofitting
Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals

---

**Suitable for**

K.x

---

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes