



6765096013



Soc.out. earth.pin+LED,enhncd contact prot.,screw-in lift term.,Q.x,green velv

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Green  
RAL code 6029  
Surface finish Velvety  
Material Duroplastic  
Treatment Untreated

**Dimensions**

Height 71 mm  
Width 71 mm  
Built-in depth 32 mm

**Installation, mounting**

Mounting on Flush mounting

**Connectivity**

Type of connection Screw terminal  
Mounting type Screw mounting  
Claw mounting

**Equipment**

Connector/plug type socket outlet Earthing pin  
Rotated central insert No  
With hinged lid No  
With round protective earth pin Yes  
With signal lamp No  
With lock No

**Accessories**

Has labelling field No

**Capacity**

Number of modules 1

**Controls and indicators**

Type of lighting for the installation devices Integrated operating control light

**Safety**

With enhanced contact protection Yes  
Ingress Protection (IP) class IP20

**Functions**

With orientation lighting No  
With function lighting Yes

**Identification**

With imprint No

**Texts**

Cover Central cover plate  
Protection Enhanced contact protection  
Type of connection With screw-in lift terminals

---

**Suitable for**

Q.x

---

**Sustainability**

---

REACH-SVHC free

Yes

---

RoHS conform

Yes

---