



6765096014



Soc.out. earth.pin+LED,enhncd contact prot.,screw-in lift term.,Q.x,orange velv

#### Technical Features

##### Voltage

Rated voltage 250 V

##### Electric current

Rated current 16 A

##### Frequency

Frequency 50 - 60 Hz

##### Materials

Colour Orange

RAL code 2003

Surface finish Velvety

Material Duroplastic

Treatment Untreated

##### Dimensions

Height 71 mm

Width 71 mm

Built-in depth 32 mm

##### Installation, mounting

Mounting on Flush mounting

##### Connectivity

Type of connection Screw terminal

Mounting type Screw mounting  
Claw mounting

##### Equipment

Connector/plug type socket outlet Earthing pin

Rotated central insert No

With hinged lid No

With round protective earth pin Yes

With signal lamp No

With lock No

##### Accessories

Has labelling field No

##### Capacity

Number of modules 1

##### Controls and indicators

Type of lighting for the installation devices Integrated operating control light

##### Safety

With enhanced contact protection Yes

Ingress Protection (IP) class IP20

##### Functions

With orientation lighting No

With function lighting Yes

##### Identification

With imprint No

##### Texts

Cover Central cover plate

Protection Enhanced contact protection

Type of connection With screw-in lift terminals

---

**Suitable for**

Q.x

---

**Sustainability**

---

REACH-SVHC free

Yes

---

RoHS conform

Yes

---