




3315402089



VGA soc. out., R.1/R.3, p. white glossy

Technical Features

Connection

Connector/plug type	VGA
Number of connections	1

Frequency

Frequency video	160 MHz
-----------------	---------

Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Metal Plastic
Treatment	Untreated

Dimensions

Height	71 mm
Width	71 mm
Depth	23.50 mm
Built-in depth flush-mounted boxes	14 mm
Built-in depth	12 mm

Connectivity

Mounting type	Screw mounting
---------------	----------------

Equipment

Shielded	Yes
With dust cover	No

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Texts

Outlet	With straight outlet
Labelling	Without labelling field
Supporting plate/supporting ring	With supporting ring

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes