



6765106086



Soc.out. earth.pin+LED orient.,enhncd contact prot.,screw-in lift ,Q1/3,ant.velv

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Anthracite

RAL code 7021

Surface finish Velvety

Material Thermoplastic

Treatment Varnished

Dimensions

Height 71 mm

Width 71 mm

Number of units 1

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal

Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet Earthing pin

Rotated central insert No

With hinged lid No

With round protective earth pin Yes

With signal lamp No

With lock No

Accessories

Has labelling field No

Capacity

Number of modules 1

Controls and indicators

Type of lighting for the installation devices Integrated orientation light

Safety

With enhanced contact protection Yes

Impact resistance IK IK05

Ingress Protection (IP) class IP20

Functions

With orientation lighting Yes

With function lighting No

Identification

With imprint No

Texts

Cover	Central cover plate
Lighting	Additional benefit by combination of a socket outlet with an orientation light
Wiring	Through-wiring possible, therefore also ideal for retrofitting
Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals

Suitable for

Q.x

Sustainability

RoHS conform	Yes
--------------	-----