



3315402045



VGA soc. out., R.1/R.3, black glossy

#### Technical Features

##### Connection

Connector/plug type	VGA
Number of connections	1

##### Frequency

Frequency video	160 MHz
-----------------	---------

##### Materials

Colour	Black
RAL code	9005
Surface finish	Glossy
Material	Metal Plastic
Treatment	Untreated

##### Dimensions

Height	71 mm
Width	71 mm
Depth	23.50 mm
Built-in depth flush-mounted boxes	14 mm
Built-in depth	12 mm

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Equipment

Shielded	Yes
With dust cover	No

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Texts

Outlet	With straight outlet
Labelling	Without labelling field
Supporting plate/supporting ring	With supporting ring

##### Suitable for

R.x	
-----	--

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes