



6768777103

Soc.out. earthing pin+hinged cover, enhncd contact prot., K.5, al., al. anodised

#### Technical Features

##### Voltage

Rated voltage	250 V
---------------	-------

##### Electric current

Rated current	16 A
---------------	------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Materials

Colour	Aluminium
RAL code	9006
Surface finish	Matt
Material	Aluminium
Treatment	Anodised

##### Dimensions

Height	71 mm
Width	71 mm
Number of units	1
Built-in depth flush-mounted boxes	35 mm
Built-in depth	31.20 mm

##### Connection

Connector/plug type	Plug-in terminal
---------------------	------------------

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting Claw mounting

##### Equipment

Connector/plug type socket outlet	Earthing pin
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	Yes
With signal lamp	No
With lock	No

##### Accessories

Has labelling field	No
---------------------	----

##### Cover, door

Type of lid	Hinged cover falls back, can be arrested in end position
-------------	--

##### Capacity

Number of modules	1
-------------------	---

##### Safety

With enhanced contact protection	Yes
Impact resistance IK	IK07
Ingress Protection (IP) class	IP20

##### Functions

With orientation lighting	No
With function lighting	No

---

**Texts**

Imprint	With imprint
Cover	Central cover plate
Protection	Enhanced contact protection
Type of connection	With plug-in terminals

---

**Suitable for**

K.x

---

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes