



6768766014

Soc. out. earthing pin, enhncl contact prot., Q.x, orange velvety

**Technical Features**

**Electric current**

Rated current	16 A
---------------	------

**Voltage**

Rated voltage	250 V
Nominal voltage	250 - 250 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Orange
RAL code	2003
Surface finish	Velvety
Material	Duroplastic
Treatment	Untreated

**Dimensions**

Height	71 mm
Width	71 mm
Built-in depth flush-mounted boxes	31 mm
Built-in depth	32 mm

**Connection**

Connector/plug type	Plug-in terminal
---------------------	------------------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Type of connection	Plug-in connection
Mounting type	Screw mounting Claw mounting

**Equipment**

Connector/plug type socket outlet	Earthing pin
Rotated central insert	No
With hinged lid	No
With round protective earth pin	Yes
With signal lamp	No
With lock	No

**Accessories**

Has labelling field	No
---------------------	----

**Capacity**

Number of modules	1
-------------------	---

**Safety**

With enhanced contact protection	Yes
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

**Functions**

With orientation lighting	No
With function lighting	No

**Texts**

Imprint	Without imprint
Cover	Central cover plate

# Product Datasheet

6768766014

---

## Texts

Protection	Enhanced contact protection
Type of connection	With plug-in terminals

## Suitable for

Q.x
-----

## Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes