



6765757004

Soc.out. earth. pin, enhncd contact prot.,screw-in lift term.,K.5,steel m.finish

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Stainless steel
RAL code 9022
Surface finish Matt
Material Metal
Stainless steel

Dimensions

Height 71 mm
Width 71 mm
Number of units 1
Built-in depth flush-mounted boxes 31 mm
Built-in depth 32 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal
Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet Earthing pin
Rotated central insert No
With hinged lid No
With round protective earth pin Yes
With signal lamp No
With lock No

Accessories

Has labelling field No

Capacity

Number of modules 1

Safety

With enhanced contact protection Yes
Impact resistance IK IK07
Ingress Protection (IP) class IP20

Functions

With orientation lighting No
With function lighting No

Identification

With imprint No

Texts

Cover Central cover plate
Protection Enhanced contact protection
Type of connection With screw-in lift terminals

Suitable for

K.x

Sustainability

REACH-SVHC free

Yes

RoHS conform

Yes
