



6765757003

Soc.out. earth.pin,enhncd contact prot.,screw-in lift term.,K.5,al. anodised

Technical Features

Electric current

Rated current	16 A
---------------	------

Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Aluminium
RAL code	9006
Surface finish	Matt
Material	Aluminium
Treatment	Anodised

Dimensions

Height	71 mm
Width	71 mm
Number of units	1
Built-in depth flush-mounted boxes	31 mm
Built-in depth	32 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting Claw mounting

Equipment

Connector/plug type socket outlet	Earthing pin
Rotated central insert	No
With hinged lid	No
With round protective earth pin	Yes
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	1
-------------------	---

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK07
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	No

Texts

Imprint	Without imprint
Cover	Central cover plate
Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals

Suitable for

K.x

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes