



6765097015



Soc.out. earth.pin+control LED,enhncd contact prot.,screw-in lift term.,K1,red

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Red
RAL code 3003
Surface finish Glossy
Material Thermoplastic
Treatment Untreated

Dimensions

Height 71 mm
Width 71 mm
Built-in depth 32 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal
Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet Earthing pin
Rotated central insert No
With hinged lid No
With round protective earth pin Yes
With signal lamp No
With lock No

Accessories

Has labelling field No

Capacity

Number of modules 1

Controls and indicators

Type of lighting for the installation devices Integrated operating control light

Safety

With enhanced contact protection Yes
Ingress Protection (IP) class IP20

Functions

With orientation lighting No
With function lighting Yes

Identification

With imprint No

Texts

Cover Central cover plate
Protection Enhanced contact protection
Type of connection With screw-in lift terminals

Suitable for

K.x

Sustainability

RoHS conform

Yes
