




3315406089



### VGA soc. out., Q.x, p. white velvety

#### Technical Features

##### Connection

|                       |     |
|-----------------------|-----|
| Connector/plug type   | VGA |
| Number of connections | 1   |

##### Frequency

|                 |         |
|-----------------|---------|
| Frequency video | 160 MHz |
|-----------------|---------|

##### Materials

|                |                  |
|----------------|------------------|
| Colour         | Polar white      |
| RAL code       | 9010             |
| Surface finish | Velvety          |
| Material       | Metal<br>Plastic |
| Treatment      | Untreated        |

##### Dimensions

|                                    |          |
|------------------------------------|----------|
| Height                             | 71 mm    |
| Width                              | 71 mm    |
| Depth                              | 23.50 mm |
| Built-in depth flush-mounted boxes | 14 mm    |
| Built-in depth                     | 12 mm    |

##### Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

##### Equipment

|                 |     |
|-----------------|-----|
| Shielded        | Yes |
| With dust cover | No  |

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
| Impact resistance IK          | IK02 |

##### Texts

|                                  |                         |
|----------------------------------|-------------------------|
| Outlet                           | With straight outlet    |
| Labelling                        | Without labelling field |
| Supporting plate/supporting ring | With supporting ring    |

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |