



3315416089



VGA soc. out., screw-in lift terminals, Q.x, p. white velvety

Technical Features

Connection

Connector/plug type	VGA
Conductor cross-section	1.50 - 1.50 mm ²
Number of connections	1

Frequency

Frequency video	160 MHz
-----------------	---------

Materials

Colour	Polar white
RAL code	9010
Surface finish	Velvety
Material	Metal Plastic
Treatment	Untreated

Dimensions

Height	71 mm
Width	71 mm
Depth	23.50 mm
Built-in depth flush-mounted boxes	13 mm

Connectivity

Mounting type	Screw mounting
---------------	----------------

Equipment

Shielded	Yes
With dust cover	No

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

Texts

Outlet	With straight outlet
Labelling	Without labelling field
Supporting plate/supporting ring	With supporting ring

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes