




3315426089



High definition soc. out., Q.x, p. white velvety

Technical Features

Connection

|                       |      |
|-----------------------|------|
| Connector/plug type   | HDMI |
| Number of connections | 1    |

Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 85 Hz |
|-----------|------------|

Materials

|                |                  |
|----------------|------------------|
| Colour         | Polar white      |
| RAL code       | 9010             |
| Surface finish | Velvety          |
| Material       | Metal<br>Plastic |
| Treatment      | Untreated        |

Dimensions

|                                    |          |
|------------------------------------|----------|
| Height                             | 71 mm    |
| Width                              | 71 mm    |
| Depth                              | 28.30 mm |
| Built-in depth flush-mounted boxes | 18 mm    |
| Built-in depth                     | 16.80 mm |

Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Equipment

|                 |     |
|-----------------|-----|
| Shielded        | Yes |
| With dust cover | No  |

Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
| Impact resistance IK          | IK02 |

Texts

|                                  |                         |
|----------------------------------|-------------------------|
| Outlet                           | With straight outlet    |
| Labelling                        | Without labelling field |
| Supporting plate/supporting ring | With supporting ring    |

Suitable for

|     |  |
|-----|--|
| Q.x |  |
|-----|--|

Sustainability

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |