



6765096015



Soc.out. earth.pin+LED,enhncd contact prot.,screw-in lift term.,Q.x,red velv

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Red

RAL code 3003

Surface finish Velvety

Material Duroplastic

Treatment Untreated

**Dimensions**

Height 71 mm

Width 71 mm

Built-in depth 32 mm

**Installation, mounting**

Mounting on Flush mounting

**Connectivity**

Type of connection Screw terminal

Mounting type Screw mounting  
Claw mounting

**Equipment**

Connector/plug type socket outlet Earthing pin

Rotated central insert No

With hinged lid No

With round protective earth pin Yes

With signal lamp No

With lock No

**Accessories**

Has labelling field No

**Capacity**

Number of modules 1

**Controls and indicators**

Type of lighting for the installation devices Integrated operating control light

**Safety**

With enhanced contact protection Yes

Ingress Protection (IP) class IP20

**Functions**

With orientation lighting No

With function lighting Yes

**Identification**

With imprint No

**Texts**

Cover Central cover plate

Protection Enhanced contact protection

Type of connection With screw-in lift terminals

---

**Suitable for**

Q.x

---

**Sustainability**

---

REACH-SVHC free

Yes

---

RoHS conform

Yes

---