



28826084

Loudspeaker Q.x alu velvety lacquered

Technical Features

Resistance

Impedance 4 Ω

Frequency

Frequency 170 - 18000 Hz

Dimensions

Built-in depth 35 mm

Materials

Colour Aluminium

Surface finish Velvety

Treatment Varnished

Power

Music power handling 4 W

Texts

Installation mode Without spreader claws

Sustainability

REACH-SVHC free Yes

RoHS conform Yes