



28826084

**Loudspeaker Q.x alu velvety lacquered**

**Technical Features**

**Resistance**

Impedance 4  $\Omega$

**Frequency**

Frequency 170 - 18000 Hz

**Dimensions**

Built-in depth 35 mm

**Materials**

Colour Aluminium

Surface finish Velvety

Treatment Varnished

**Power**

Music power handling 4 W

**Texts**

Installation mode Without spreader claws

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes