



6765091909



Soc.out. earth.pin+LED,enhncd contact prot.,screw-in lift term.,S1/B3/7,wh

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Polar white

RAL code 9010

Surface finish Matt

Material Thermoplastic

Treatment Untreated

**Dimensions**

Height 71 mm

Width 71 mm

Built-in depth flush-mounted boxes 31 mm

Built-in depth 32 mm

**Installation, mounting**

Mounting on Flush mounting

**Connectivity**

Type of connection Screw terminal

Mounting type Screw mounting  
Claw mounting

**Equipment**

Connector/plug type socket outlet Earthing pin

Rotated central insert No

With hinged lid No

With round protective earth pin Yes

With signal lamp No

With lock No

**Accessories**

Has labelling field No

**Capacity**

Number of modules 1

**Controls and indicators**

Type of lighting for the installation devices Integrated operating control light

**Safety**

With enhanced contact protection Yes

Ingress Protection (IP) class IP20

**Functions**

With orientation lighting No

With function lighting Yes

**Identification**

With imprint No

---

**Texts**

Cover	Central cover plate
Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals

---

**Suitable for**

S.x/B.x

---

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes