



6765092045



Soc.out. earth.pin+LED,enhncd contact prot.,screw-in lift term.,R.1.3,bl.

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Black
RAL code 9005
Surface finish Glossy
Material Thermoplastic
Treatment Untreated

Dimensions

Height 71 mm
Width 71 mm
Number of units 1
Built-in depth 32 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal
Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet Earthing pin
Rotated central insert No
With hinged lid No
With round protective earth pin Yes
With signal lamp No
With lock No

Accessories

Has labelling field No

Capacity

Number of modules 1

Controls and indicators

Type of lighting for the installation devices Integrated operating control light

Safety

With enhanced contact protection Yes
Impact resistance IK IK05
Ingress Protection (IP) class IP20

Functions

With orientation lighting No
With function lighting Yes

Identification

With imprint No

Texts

Cover	Central cover plate
Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals

Suitable for

R.x

Sustainability

RoHS conform	Yes
--------------	-----