



WMDP50VN_OV

50A Double Pole Switch 2 Gang Vertical with LED Indicator Marked OVEN

Technical Features

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Colour White

Surface finish Glossy

Material Urea formaldehyde

Treatment Untreated

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 86 x 86 mm

Built-in depth 22.60 mm

Electric current

Rated current 50 A

Texts

Lighting With control LED for ON

Push button No

Imprint With clear terminal markings