



WMGSDP2B\_HW

**20A 1 Way Double Pole Switch Marked 'HOT WATER' Black**

**Technical Features**

**Electric current**

Switching current 20 A

**Installation, mounting**

Mounting on Flush mounting

**Voltage**

Rated voltage 250 V

**Materials**

Colour Black

Surface finish Glossy

Material Urea formaldehyde

Treatment Untreated

**Identification**

Assembly arrangement Basic element with central cover plate

**Connectivity**

Mounting type Snap-on mounting

**Controls and indicators**

Number of buttons 1

**Dimensions**

Dimensions 59 x 25 mm

Built-in depth 13.10 mm

**Safety**

Ingress Protection (IP) class IP20

**Architecture**

Control/operation element Single rocker

**Electric current**

Rated current 20 A

**Texts**

Lighting Without lighting (cannot be illuminated)

Switch mode 2-pole

**Sustainability**

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes