



PCR2000!1.0LSF!3

PCR2000 c/w 3 Core 1.00mm² 3m LS0H Lead

Technical Features

Architecture

Number of poles	3
-----------------	---

Voltage

Max. operating voltage	240 V
------------------------	-------

Electric current

Rated current	6 A
---------------	-----

Cable

Cable diameter	7 mm
----------------	------

Cable length	3 m
--------------	-----

Dimensions

Length	3000 mm
--------	---------

Connection

Conductor cross-section	1 - 1 mm ²
-------------------------	-----------------------

Equipment

Mechanical coding	Yes
-------------------	-----

Type cable side 1	Plug
-------------------	------

Type cable side 2	Free conductor end
-------------------	--------------------

Type of cable	Device connection cable
---------------	-------------------------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

Materials

Colour	White
--------	-------

Cable

Cable permanent temperature resistant to	90 °C
--	-------

Sustainability

RoHS conform	Yes
--------------	-----