



WMGKSB!EL

**20A Double Pole Key Switch Marked 'EM LTG TEST' Black**

**Technical Features**

**Electric current**

|                           |      |
|---------------------------|------|
| Momentary contact current | 10 A |
|---------------------------|------|

**Voltage**

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

**Architecture**

|                           |               |
|---------------------------|---------------|
| Control/operation element | Single rocker |
| Number of poles           | 2             |

**Materials**

|                |                   |
|----------------|-------------------|
| Colour         | White             |
| Surface finish | Glossy            |
| Material       | Urea formaldehyde |
| Treatment      | Untreated         |
| Transparent    | No                |

**Dimensions**

|        |       |
|--------|-------|
| Height | 60 mm |
| Width  | 25 mm |
| Depth  | 24 mm |

**Installation, mounting**

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

**Controls and indicators**

|                              |    |
|------------------------------|----|
| Number of buttons            | 0  |
| With feedback signal contact | No |

**Connectivity**

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Accessories**

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

**Texts**

|          |                   |
|----------|-------------------|
| Imprint  | With imprint      |
| Lighting | Without neon lamp |

**Suitable for**

|          |  |
|----------|--|
| sollysta |  |
|----------|--|

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |