



CR64AX/1.0LSF/5

CR64AX c/w 4 Core 1mm² 5m LSOH Lead

Technical Features

Architecture

Number of poles	4
-----------------	---

Voltage

Max. operating voltage	240 V
------------------------	-------

Electric current

Rated current	6 A
---------------	-----

Cable

Cable diameter	8 mm
Cable length	5 m

Dimensions

Length	5000 mm
--------	---------

Connection

Conductor cross-section	1 - 1 mm ²
-------------------------	-----------------------

Equipment

Mechanical coding	Yes
Type cable side 1	Plug
Type cable side 2	Free conductor end
Type of cable	Device connection cable

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

Materials

Colour	White
--------	-------

Cable

Cable permanent temperature resistant to	90 °C
--	-------