



P22!LSF!1.0

P22 c/w 3 Core 1.00mm² 4 Metre LSOH Lead

Technical Features

Architecture

Number of poles 2

Voltage

Max. operating voltage 240 V

Electric current

Rated current 6 A

Dimensions

Length 4000 mm

Connection

Conductor cross-section 1 - 1 mm²

Equipment

Mechanical coding Yes

Type cable side 1 Plug

Type cable side 2 Free conductor end

Type of cable Device connection cable

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2 2

Materials

Colour White

Cable

Cable permanent temperature resistant to 90 °C

Sustainability

REACH-SVHC free Yes

RoHS conform Yes