



WMGSDP2_OL

20A 1 Way Double Pole Switch Marked 'OUTSIDE LIGHT'

Technical Features

Electric current

Switching current	20 A
-------------------	------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	White
--------	-------

Surface finish	Glossy
----------------	--------

Material	Urea formaldehyde
----------	-------------------

Treatment	Untreated
-----------	-----------

Identification

Assembly arrangement	Basic element with central cover plate
----------------------	--

Connectivity

Mounting type	Snap-on mounting
---------------	------------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	59 x 25 mm
------------	------------

Built-in depth	18.70 mm
----------------	----------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Architecture

Control/operation element	Single rocker
---------------------------	---------------

Electric current

Rated current	20 A
---------------	------

Texts

Lighting	With control LED for ON
----------	-------------------------

Switch mode	2-pole
-------------	--------

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----