




WMSSU83N/HB

**13A FCU Switched with LED Indicator Marked HOB**

**Technical Features**

**Installation, mounting**

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

**Voltage**

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

**Materials**

|                |                   |
|----------------|-------------------|
| Colour         | White             |
| Surface finish | Glossy            |
| Material       | Urea formaldehyde |
| Treatment      | Untreated         |

**Identification**

|                      |                                     |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

**Connectivity**

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

**Controls and indicators**

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

**Dimensions**

|                |            |
|----------------|------------|
| Dimensions     | 86 x 86 mm |
| Built-in depth | 25.30 mm   |

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Electric current**

|               |      |
|---------------|------|
| Rated current | 13 A |
|---------------|------|

**Texts**

|                   |                                            |
|-------------------|--------------------------------------------|
| Installation mode | For flush-mounted and hollow wall mounting |
| Lighting          | With control LED for ON                    |
| Switch mode       | 2-pole                                     |

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|