



WMGSDP2N_OV

20A 1 Way Double Pole Switch with LED Indicator Marked 'OVEN'

Technical Features

Electric current

Switching current	20 A
-------------------	------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

Identification

Assembly arrangement	Basic element with central cover plate
----------------------	--

Connectivity

Mounting type	Snap-on mounting
---------------	------------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	59 x 25 mm
Built-in depth	13.10 mm

Electric current

Rated current	20 A
---------------	------

Texts

Lighting	With control LED for ON
Push button	No
Imprint	With clear terminal markings

Sustainability

RoHS conform	Yes
--------------	-----