



PCR2000!LSF!1.0

**PCR2000 c/w 3 Core 0.75mm<sup>2</sup> 1m LS0H Lead**

**Technical Features**

**Architecture**

|                 |   |
|-----------------|---|
| Number of poles | 3 |
|-----------------|---|

**Voltage**

|                        |       |
|------------------------|-------|
| Max. operating voltage | 240 V |
|------------------------|-------|

**Electric current**

|               |     |
|---------------|-----|
| Rated current | 6 A |
|---------------|-----|

**Cable**

|                |      |
|----------------|------|
| Cable diameter | 7 mm |
|----------------|------|

**Dimensions**

|        |         |
|--------|---------|
| Length | 1000 mm |
|--------|---------|

**Connection**

|                         |                             |
|-------------------------|-----------------------------|
| Conductor cross-section | 0.75 - 0.75 mm <sup>2</sup> |
|-------------------------|-----------------------------|

**Equipment**

|                   |                         |
|-------------------|-------------------------|
| Mechanical coding | Yes                     |
| Type cable side 1 | Plug                    |
| Type cable side 2 | Free conductor end      |
| Type of cable     | Device connection cable |

**Use conditions**

|  |   |
|--|---|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
|--|---|

**Materials**

|        |       |
|--------|-------|
| Colour | White |
|--------|-------|

**Cable**

|  |       |
|--|-------|
| Cable permanent temperature resistant to | 90 °C |
|--|-------|

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|