



K7J1M075W

6A Luminaire Lead 1.5m 0.75mm 4 Core Plug to Wire

Technical Features

Architecture

Number of poles	3
-----------------	---

Voltage

Max. operating voltage	240 V
------------------------	-------

Electric current

Rated current	6 A
---------------	-----

Cable

Cable diameter	8 mm
----------------	------

Connection

Conductor cross-section	0.75 - 0.75 mm ²
-------------------------	-----------------------------

Equipment

Mechanical coding	Yes
Type cable side 1	Plug
Type cable side 2	Free conductor end
Type of cable	Device connection cable

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

Materials

Colour	White
--------	-------

Cable

Cable permanent temperature resistant to	90 °C
--	-------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes