



WMGKSIEL

### 20A Double Pole Key Switch Marked 'EM LTG TEST'

#### Technical Features

##### Electric current

|                           |      |
|---------------------------|------|
| Momentary contact current | 10 A |
|---------------------------|------|

##### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

##### Architecture

|                           |               |
|---------------------------|---------------|
| Control/operation element | Single rocker |
| Number of poles           | 2             |

##### Materials

|                |                   |
|----------------|-------------------|
| Colour         | White             |
| Surface finish | Glossy            |
| Material       | Urea formaldehyde |
| Treatment      | Untreated         |
| Transparent    | No                |

##### Dimensions

|        |       |
|--------|-------|
| Height | 60 mm |
| Width  | 25 mm |
| Depth  | 24 mm |

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Controls and indicators

|                              |    |
|------------------------------|----|
| Number of buttons            | 0  |
| With feedback signal contact | No |

##### Connectivity

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

##### Texts

|          |                   |
|----------|-------------------|
| Imprint  | With imprint      |
| Lighting | Without neon lamp |

##### Suitable for

|          |  |
|----------|--|
| sollysta |  |
|----------|--|

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |