



K7B3M15W

16A Luminaire Lead 3m 1.5mm 3 Core Plug -Wire

Technical Features

Architecture

| | |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

Voltage

| | |
|------------------------|-------|
| Max. operating voltage | 240 V |
|------------------------|-------|

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Cable

| | |
|----------------|------|
| Cable diameter | 9 mm |
|----------------|------|

Connection

| | |
|-------------------------|-----------------------------|
| Conductor cross-section | 1.50 - 1.50 mm ² |
|-------------------------|-----------------------------|

Equipment

| | |
|-------------------|-------------------------|
| Mechanical coding | Yes |
| Type cable side 1 | Plug |
| Type cable side 2 | Free conductor end |
| Type of cable | Device connection cable |

Use conditions

| | |
|--|---|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
|--|---|

Materials

| | |
|--------|-------|
| Colour | White |
|--------|-------|

Cable

| | |
|--|-------|
| Cable permanent temperature resistant to | 90 °C |
|--|-------|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |