



LFF6023009016

**Trunking LFF 60x230mm with coupling and 2 cable clips per meter traffic white**

**Technical Features**

**Dimensions**

Height	60 mm
Width	230 mm
Length	2000 mm
Inner cross-section	10998 - 10998 mm <sup>2</sup>

**Capacity**

Max. number of cables (Ø11mm, 50% filled, without devices)	58
--	----

**Materials**

Material	Polyvinylchloride (PVC)
Treatment	Untreated
RAL code	9016
Colour	Traffic white

**Safety**

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

**Use conditions**

Operating temperature	-5 - 60 °C
-----------------------	------------

**Connectivity**

Trunking coupling	Pre-equipped with couplers
-------------------	----------------------------

**Equipment**

Number of partitions	0
Number of compartments	1 - 4
Number of pluggable partitions	3
Cable retaining clip included	Yes
With protective film	No

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes