



LFF6015007030

Trunking 60150, grey with coupler and 2 cable retainer per meter

Technical Features

Dimensions

Height	60 mm
Width	150 mm
Length	2000 mm
Inner cross-section	7122 - 7122 mm ²

Capacity

Max. number of cables (Ø11mm, 50% filled, without devices)	23
--	----

Materials

Material	Polyvinylchloride (PVC)
Treatment	Untreated
RAL code	7030
Colour	Stone grey

Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

Standards

Suitable for functional integrity according to DIN4102-12	No
---	----

Use conditions

Operating temperature	-5 - 60 °C
-----------------------	------------

Connectivity

Trunking coupling	Pre-equipped with couplers
-------------------	----------------------------

Equipment

Number of partitions	0
Number of compartments	1 - 4
Number of pluggable partitions	3
Cable retaining clip included	Yes
With protective film	No

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes