



LFF6015009016

Trunking LFF 60x150mm with coupling and 2 cable clips per meter traffic white

Technical Features

Dimensions

Height	60 mm
Width	150 mm
Length	2000 mm
Inner cross-section	7122 - 7122 mm <sup>2</sup>

Capacity

Max. number of cables (Ø11mm, 50% filled, without devices)	37
--	----

Materials

Material	Polyvinylchloride (PVC)
Treatment	Untreated
RAL code	9016
Colour	Traffic white

Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

Use conditions

Operating temperature	-5 - 60 °C
-----------------------	------------

Connectivity

Trunking coupling	Pre-equipped with couplers
-------------------	----------------------------

Equipment

Number of partitions	0
Number of compartments	1 - 4
Number of pluggable partitions	3
Cable retaining clip included	Yes
With protective film	No

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes