



WXD202H

**Rocker for RJ45 socket gallery 2 modules pure-white**

**Technical Features**

**Controls and indicators**

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

**Materials**

|                |                    |
|----------------|--------------------|
| Colour         | Traffic white      |
| RAL code       | 9016               |
| Surface finish | Glossy             |
| Material       | Polycarbonate (PC) |
| Treatment      | Untreated          |

**Dimensions**

|        |         |
|--------|---------|
| Height | 45 mm   |
| Width  | 45 mm   |
| Depth  | 8.40 mm |

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

**Connection**

|                     |              |
|---------------------|--------------|
| Connector/plug type | Modular jack |
|---------------------|--------------|

**Connectivity**

|               |                |
|---------------|----------------|
| Mounting type | Click mounting |
|---------------|----------------|

**Equipment**

|                                |    |
|--------------------------------|----|
| Monitoring window/light outlet | No |
|--------------------------------|----|

**Accessories**

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP21 |
|-------------------------------|------|

**Use conditions**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -10 - 35 °C |
|-----------------------|-------------|

**Texts**

|           |                   |
|-----------|-------------------|
| Imprint   | Without imprint   |
| Labelling | Without labelling |

**Suitable for**

|         |  |
|---------|--|
| gallery |  |
|---------|--|

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |