




WXD259H

### Rocker double F socket gallery 2 modules pure-white

#### Technical Features

##### Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

##### Materials

|                |                    |
|----------------|--------------------|
| Colour         | Traffic white      |
| RAL code       | 9016               |
| Surface finish | Glossy             |
| Material       | Polycarbonate (PC) |
| Treatment      | Untreated          |

##### Dimensions

|        |         |
|--------|---------|
| Height | 45 mm   |
| Width  | 45 mm   |
| Depth  | 8.40 mm |

##### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

##### Connection

|                     |      |
|---------------------|------|
| Connector/plug type | RJ45 |
|---------------------|------|

##### Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Click mounting |
|---------------|----------------|

##### Equipment

|                                |    |
|--------------------------------|----|
| Monitoring window/light outlet | No |
|--------------------------------|----|

##### Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP21 |
| Impact resistance IK          | IK05 |

##### Use conditions

|                       |             |
|-----------------------|-------------|
| Operating temperature | -10 - 35 °C |
|-----------------------|-------------|

##### Texts

|           |                   |
|-----------|-------------------|
| Labelling | Without labelling |
|-----------|-------------------|

##### Suitable for

|         |  |
|---------|--|
| gallery |  |
|---------|--|

##### Sustainability

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |