



WMGSDP2!HB

20A 1 Way Double Pole Switch Marked 'HOB'

Technical Features

Electric current

Switching current 20 A

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Colour White

Surface finish Glossy

Material Urea formaldehyde

Treatment Untreated

Identification

Assembly arrangement Basic element with central cover plate

Connectivity

Mounting type Snap-on mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 59 x 25 mm

Built-in depth 13.10 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Single rocker

Electric current

Rated current 20 A

Texts

Lighting Without lighting (cannot be illuminated)

Switch mode 2-pole

Sustainability

REACH-SVHC free Yes

RoHS conform Yes