



WMSSU83!CTLHTG

13A FCU Switched Marked CENTRAL HEATING

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	White
--------	-------

Surface finish	Glossy
----------------	--------

Material	Urea formaldehyde
----------	-------------------

Treatment	Untreated
-----------	-----------

Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	86 x 86 mm
------------	------------

Built-in depth	25.30 mm
----------------	----------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Electric current

Rated current	13 A
---------------	------

Texts

Installation mode	For flush-mounted and hollow wall mounting
-------------------	--

Lighting	Without lighting (cannot be illuminated)
----------	--

Switch mode	2-pole
-------------	--------

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----