



P64AXI2.0

P64AX c/w 4 Core 0.75mm² 2m PVC Lead

Technical Features

Architecture

Number of poles 4

Voltage

Max. operating voltage 240 V

Electric current

Rated current 6 A

Cable

Cable length 2 m

Dimensions

Length 2000 mm

Connection

Conductor cross-section 0.75 - 0.75 mm²

Equipment

Mechanical coding Yes

Type cable side 1 Plug

Type cable side 2 Free conductor end

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2 2

Materials

Colour White

Cable

Cable permanent temperature resistant to 90 °C

Sustainability

REACH-SVHC free Yes

RoHS conform Yes