



HWY030H

UV time delay controller 24-30V AC/DC (UVTC)

Technical Features

Connection

Cross-section of input and output with screws, for massive conductors	0.6 - 2.5 mm ²
Cross-section of input and output with screws, for flexible conductors	0.6 - 2.5 mm ²

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Voltage

Command voltage AC	24 - 30 V
--------------------	-----------

Sustainability

REACH-SVHC free	Yes
-----------------	-----