
Product Datasheet
WMSSU83N/EF



WMSSU83N!EF

13A FCU Switched with LED Indicator Marked EXTRACT FAN

Technical Features

Installation, mounting

Mounting on	Flush mounting

Voltage

Rated voltage	250 V

Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

Identification

Assembly arrangement	Basic element with full cover plate

Connectivity

Mounting type	Screw mounting

Controls and indicators

Number of buttons	1

Dimensions

Dimensions	86 x 86 mm
Built-in depth	25.30 mm

Electric current

Rated current IN	13 A

Texts

Installation mode	For flush-mounted and hollow wall mounting
Lighting	With control LED for ON
Push button	No
Imprint	With clear terminal markings

Sustainability

RoHS conform	Yes