



P64AXILSF4.0

P64AX c/w 4 Core 0.75mm² 4m LSOH Lead

Technical Features

Architecture

Number of poles	4
-----------------	---

Voltage

Max. operating voltage	240 V
------------------------	-------

Electric current

Rated current	6 A
---------------	-----

Cable

Cable length	4 m
--------------	-----

Dimensions

Length	4000 mm
--------	---------

Connection

Conductor cross-section	0.75 - 0.75 mm ²
-------------------------	-----------------------------

Equipment

Mechanical coding	Yes
Type cable side 1	Plug
Type cable side 2	Free conductor end
Type of cable	Device connection cable

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
----------------------------------------------------------	---

Materials

Colour	White
--------	-------

Cable

Cable permanent temperature resistant to	90 °C
------------------------------------------	-------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes