



P64AXILSF!4.0

### P64AX c/w 4 Core 0.75mm<sup>2</sup> 4m LSOH Lead

#### Technical Features

##### Architecture

Number of poles	4
-----------------	---

##### Voltage

Max. operating voltage	240 V
------------------------	-------

##### Electric current

Rated current	6 A
---------------	-----

##### Cable

Cable length	4 m
--------------	-----

##### Dimensions

Length	4000 mm
--------	---------

##### Connection

Conductor cross-section	0.75 - 0.75 mm <sup>2</sup>
-------------------------	-----------------------------

##### Equipment

Mechanical coding	Yes
Type cable side 1	Plug
Type cable side 2	Free conductor end
Type of cable	Device connection cable

##### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

##### Materials

Colour	White
--------	-------

##### Cable

Cable permanent temperature resistant to	90 °C
--	-------

##### Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes