



K7J1M1W

**10A Luminaire Lead 1.5m 1mm 4 Core Plug to Wire**

**Technical Features**

**Architecture**

Number of poles	3
-----------------	---

**Voltage**

Max. operating voltage	240 V
------------------------	-------

**Electric current**

Rated current	10 A
---------------	------

**Cable**

Cable diameter	9 mm
----------------	------

**Connection**

Conductor cross-section	1 - 1 mm <sup>2</sup>
-------------------------	-----------------------

**Equipment**

Mechanical coding	Yes
Type cable side 1	Plug
Type cable side 2	Free conductor end
Type of cable	Device connection cable

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

**Materials**

Colour	White
--------	-------

**Cable**

Cable permanent temperature resistant to	90 °C
--	-------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes