



K7J1M1W

10A Luminaire Lead 1.5m 1mm 4 Core Plug to Wire

Technical Features

Architecture

Number of poles	3
-----------------	---

Voltage

Max. operating voltage	240 V
------------------------	-------

Electric current

Rated current	10 A
---------------	------

Cable

Cable diameter	9 mm
----------------	------

Connection

Conductor cross-section	1 - 1 mm ²
-------------------------	-----------------------

Equipment

Mechanical coding	Yes
Type cable side 1	Plug
Type cable side 2	Free conductor end
Type of cable	Device connection cable

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

Materials

Colour	White
--------	-------

Cable

Cable permanent temperature resistant to	90 °C
--	-------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes