



K7P3M1W

10A Luminaire Lead 3m 1mm 5 Core Plug to Wire

Technical Features

Architecture

Number of poles	5
-----------------	---

Voltage

Max. operating voltage	240 V
------------------------	-------

Electric current

Rated current	10 A
---------------	------

Cable

Cable diameter	10 mm
----------------	-------

Connection

Conductor cross-section	1 - 1 mm ²
-------------------------	-----------------------

Equipment

Mechanical coding	Yes
-------------------	-----

Type cable side 1	Plug
-------------------	------

Type cable side 2	Free conductor end
-------------------	--------------------

Type of cable	Device connection cable
---------------	-------------------------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

Materials

Colour	White
--------	-------

Cable

Cable permanent temperature resistant to	90 °C
--	-------

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----